

Data Sheet JetFlex[®] Disc Diffuser - HD 270

F053 J27



Installation drawing



Dimensions

Hight	Diameter total/effective	Overall height membrane top of tube	Perforated area	Orifice	Thread	Check valve
[mm]	[mm]	[mm]	[m²]	[mm]		
60	268/218	30	0,037	8	R 3/4″	On request.

Air flow

Air flow rates at standard operation conditions	max overload/ maintenance air flow rate	Operating temperature	Operation mode	Application
[m _N ³ /h]	$[m_N^3/h]$	[°C]		
2-6	10	0 - 80	intermittent continuous	municipal waste water

 \cdot Shutdown of operation is highly recommended for air flow rates lower than minimum rate.

 \cdot Overload air flow rate (e.g. cleaning) should not be applied longer than 10 min/day.

• Numbers are for guidance only. Operating diffusers at too high or too low an airflow rate may reduce lifetime or performance. See Technical Report `Slit size for aeration membranes' for details.



Туре	Permitted wall thick- ness of header tube drilled hole		Material	Colour
	[mm]	[mm]		
Universal Saddle PVC-Saddle 90 mm PVC-Saddle 110 mm	2 - 8	31,8 (1 1/4″) 35 35	EPDM 75 Sh A PVC PVC	Black White/Black White/Black

Connectors to header pipe

Membrane material

Type Colour		F053 EPDM Black
Polymer Carbon black Plasticiser Others		33 % 31 % 33 % 3 %
Density Tensile strength Elongation at break Tear strength Hardness Tension set	DIN EN ISO 1183-1:2004 DIN 53504 DIN 53504 DIN ISO 34-1:2004 DIN 53505; ASTM D 624 B DIN ISO 2285:2003-0753505 100 % Elongation; 24 h, RT	1,08 ±0,03 g/cm ³ > 10 N/mm ² > 400% > 7 N/mm 53 ± 5 Shore A < 5%
Ozone resistance	DIN 53509	zero cracks

Support plate material

Material	Colour	Additional colours	Logo
PP GF 30	Black	On request.	On request.

Shipping unit

Shipping unit	Dimensions L x W x H	Unit weight	Unit per pallet	Pallet size	Pallet weight
	[mm]	[kg]		[mm]	[kg]
50 pcs./ cardboard	800 x 600 x 360	approx 35	1, 2, 3	max 800 x 600 x 1200	max 117
50 pcs./ cardboard	800 x 600 x 360	approx 35	2, 4, 6, 8	max 1200 x 800 x 1550	max 287



Standard oxygen transfer effciency (SOTE) and headloss for HD 270 F053 J27



Water depth	4,50 m	1	tap water	
Submergence depth	4,20 m		bubble column	
Atmospheric pressure Water temperature	1.013 hPa 16,3 ● C	Tank volume5,09 rTank floor area1,13 r $C_{ss,r}$ 9,81 m	m^2	

Test conditions SOTE acc. to German Standard DWA M 209 (desorption method) Certifcate ISAH, University Hanover, mea suring tolerance +/- 1% Headloss internal tests tole rances +/- 5%

Storage:

Diffuser and/or rubber sleeves must be stored factory-packed in a dark, dry, ventilated and dust-free storage space according to DIN 7716. Avoid frost, heat, UV/radiation, dust and working which can cause damage of diffuser and/or packing. Do not store outdoors! The storage of rubber parts until installation/starting operation should not exceed one year. At on-site delivery, all rubber and plastic parts must be stored in their original packaging. Crates exposed to direct sunlight must be covered with tarpaulin to protect against UV-radiation.

Maintenance:

Diffusers can only be checked, if the activated sludge tank is out of work and empty. That is why normal cleaning must be done at work. Formic acid is used very successfully against carbonating. To keep the pores open, formic acid is sprayed into the com - pressed air for a short time. Also a regular use with maximum air fow for a short time helps keep the diffuser in good conditions for a long time. (refer to Maintenance Manual)

Membrane lifetime:

Lifetime is depending on waste water infuent, plant design, operation conditions and preventive main tenance measures. Reference plants have achieved more than 5 year in municipal waste water. Please refer to our standard warranty terms and conditions which can downloaded from our website.

Disclaimer: This information is based on our present state of knowledge and is intended to provide general notes on our products and their uses. It should not therefore be construed as guaranteeing specific properties of the products described or their suitability for a particular application. Any existing industrial property rights must be observed. The quality of our products is guaranteed under our General Condition of Sale.



